GRAPHTEC

General Purpose Data Acquisition System

Modular

DATA PLATFORM GL7000

Touch Panel Control On-Demand Signal Acquisition Embedded Monitoring and Datalogging Solution



Attach up to 10 input/outport modules in a mixed signal environment

Corresponds to various measurement types (physical, mechanical, and electrical)

Supports a variety of storage media including an SSD module with a capacity of 128GB

Standalone Data Acquisition Platform with Embedded Option

Allows up to 112 channels in one main unit by attaching up to 10 units of the input / output modules.*1 Detachable display module enables the GL7000 to be used in a stand-alone platform or to be embedded in a test system. Control and monitor via the PC or display module may be done independently.

Alarm output terminal (included in the main module)



MODULE OPTIONS (8 TOTAL) - Compatible with various electrical, mechanical, and physical measurement needs.

Voltage	Volt./Temp.	High-speed	High Voltage
Module	Module	Voltage Module	Module
GL7-V	GL7-M	GL7-HSV	GL7-HV
DC Strain	Charge	Voltage Output	Logic/Pulse
Module	Module	Module	Module
GL7-DCB	GL7-CHA	GL7-DC0	GL7-L/P


LAN straight cable (CAT5 or higher class, length up to 10m) allows an extended display option for:





Maintains the maximum sampling speed even when the number of input/output modules are increased *1

• Each of the 10 units can include a different input/output module * 2




. Up to 10 input/output modules of the same kind can be attached to one main unit




Dual-Sampling Feature (Firmware version 2.0 or later)

Dual sampling speed can now be configured at the same time. While recording long intervals on the slow sampling speed, trigger set can start recording dynamic transient signals at a fast sampling speed.



Up to 10 input/output modules can be attached to one main unit *2



- Maximum sampling speed will depend on the data destination.
 - (RAM and optional SSD module is the fastest, Flash memory, SD Card will be slower.)
- 2. If different types of modules are attached,
 - the effective sampling speed of the system meets the fastest sampling
 - speed among the installed modules.
 - When the maximum sampling speed of the module is slower than the maximum sampling speed of the fastest amplifier, signal will be sampled with maximum sampling speed of the module. The same data is saved with the system sampling speed until new data is captured on the
 - The number of modules that can be attached is limited by the type of module. Up to 10 modules (maximum 112ch with 7 GL7-L/P module, max 100ch with GL7-V or GL7-M module).
 - For Logic/Pulse module (GL7-L/P): Maximum 7 units allowed using logic option (112ch).
 - Maximum 2 units allowed using pulse option (32ch). (The mode for logic or pulse can be set for each unit.) For Strain module (GL7-DCB):
 - Maximum 8 units allowed with additional two other amplifier units. (Number of channels is limited to 112ch.)
 - · For the logic/pulse module, the number of channels can be limited by the selected sampling speed when the module is attached together with other amplifier modules.
 - 1µs sampling interval : up to 8 channels 2µs sampling interval : up to 16 channels (If two modules are attached, channel #1 to #8 in each unit can be used.) When pulse mode is used, the maximum sampling speed is the 100us. The data will be updated every 100us.

Touch Panel Display Option (GL7-DISP)

The display unit incorporates a touch panel system to provide convenient on-site operation

Touch the icon, move to the next setting menu screen.





Function menu icons (Firmware version 2.0 or later)

The display unit can be separated from the main unit with a LAN cable



Four Different Display Methods

Each of the 10 units can include a different input/output module *2



- Available when the destination of data file is the Built-in flash memory / SD memory card / SSD unit (optional). Sampling interval should be the 100ms or

- Select two functions from the Ave. / Max. / Min. / Peak value and Off
- Sampling interval should be 100ms or longer.







Supports multiple types of storage

Built-in RAM

RAM is built into each of the amplifier modules to allow recording of up to 2 million samples. Increasing the number of channels does not decrease the data capture duration.

3 SD memory card

SD card slot (supports SDHC, up to 32GB) is standard on the main module. Captured data can be saved directly on the SD card when sampling speed is slower than 1ms (sampling speed: 1 k Samples/s). Supports hot-swap where SD memory card can be replaced during recording without any data loss. The captured data can be transferred easily to the PC during offline condition.

* The hot-swap is possible when the sampling is slower than 100ms.

2 Built-in Flash memory

4GB of Flash memory is built into the main module. Captured data can be saved directly to the flash memory when sampling speed is less than 1ms (1k Samples/s). Non-volatile memory (saved data is retained even if the power is turned off).

* The storage capacity might differ by its production date.

4 SSD module (128GB)

Allows multiple recording of large amount of data to be saved when optional SSD module is used. It has a high vibration resistance and the captured data can be saved directly to the SSD when sampling is not faster than 1µs.



GL7-SSD SSD module needs to be set next to the main module.

Advantage of SSD • Retain the data even when power is off • High vibration resistance • High-speed access

* The number of modules are limited.

Maximum sampling speed and the data capturing time *1

		Number of units, Max. sampling speed (interval)		Capturing time when single module is attached (when 10 modules are attached)					
Input Module	Strage Device	Attached to 1 or 2 modules	Attached to 3 or 4 modules	Attached to 5 to 10 modules	1MS/s (1µs)	100KS/s (10μs)	1KS/s (1ms)	1005/s (10ms)	1S/s (1s)
High-speed	Built-in RAM (2Msamples)		1M5/s (1µs)	*	2sec. (2sec.)	20sec. (20sec.)	33min. (33min.)	5hrs. (5hrs.)	23days (23days)
Voltage	Built-in Flash memory (4GB)	1k5/s (1ms)		N/A	N/A	72hrs. (10hrs.)	32days (4days)	3269days (440days)	
Module	SD memory card (32GB)*2					83hrs, (11hrs.)	34days (4days)	3605daws (670daws)	
Piodole	SSD (128GB)*2	1MS/s (1µs)	500KS/s (2µs)	200KS/s (5µs)	4min. (N/A)	44min. (6min.)	OSHS. (HHS.)	34days (4days)	3495days (470days)
	Built-in RAM (2Msamples)		1MS/s (1µs)		2sec. (2sec.)	20sec. (20sec.)	33min. (33min.)	5hrs. (5hrs.)	23days (23days)
High Voltage	Built-in Flash memory (4GB)		11/6 (c (1mc)		N/A	109hrs. (17hrs.)	45days (7days)	4577days (715days)	
Module	SD memory card (32GB)*2	1kS/s (1ms)		N/A	N/A	117hrs. (18hrs.)	48days (7days)	4893days (764days)	
	SSD (128GB)*2	1MS/s (1µs)	500KS/s (2µs)	200KS/s (5µs)	4min. (N/A)	44min. (11min.)	Tivius. (toms.)	Houdy's (7udy's)	4693uays (764uays)
DCStrain*3	Built-in RAM (2Msamples)	100kS/s (10µs)		N/A	20sec. (20sec.)	33min. (33min.)	5hrs. (5hrs.)	23days (23days)	
	Built-in Flash memory (4GB)	NE (a (lone)				72hrs. (13hrs.)	32days (5days)	3269days (544days)	
&Charge	SD memory card (3GB)*2	1kS/s (1ms)			N/A	83hrs. (13hrs.)	36 days (Edays)	3495days (582days)	
Module	4odule SSD (128GB)*2		100kS/s (10µs)		44min. (6min.)		Bants, (Tarits.)	34days (5days)	3475uays (562uays)
	Built-in RAM (2M samples)						33min. (33min.)	5hrs. (5hrs.)	23days (23days)
Voltage	Built-in Flashmemory (4GB)	1kS/s (1ms)		N/A	N/A	42hrs. (4hrs.)	17days (2days)	1760days (204days)	
Module	SD memory card (32GB)*2					45hrs. (5hrs.)	18days (2days)	1882days (218days)	
	SSD (128GB)*2								
	Built-in RAM (2Msamples)	1005/s (10ms)		N/A	N/A	N/A	5hrs. (5hrs.)	23days (23days)	
Volt./Temp.	Built-in Flash memory (4GB)						17days (2days)	1760days (204days)	
Module	SD memory card (32GB)*2						18days (2days)	1882days (218days)	
	SSD (128GB)*2	1					loudys (zudys)	loozudys (z loudys)	

- *1 Capturing time values (approximate data) are saved as GBD format files. When data is saved in CSV format, maximum sampling speed will be 10ms regardless of the captured destination and module type. Value of the capturing time is also different from above. (Data cannot be saved to built-in RAM using the CSV format.)
 *2 The file size of the captured data is limited up to 46B on firmware version 2.0 alter, 26B on firmware version 1.6 or before.
 *3 Reference recording time is for up to 8 modules, (max 6L7-DCB and 6L7-CHA modules is 8.)

Useful functions for data saving and replay

- SD memory card hot swap
- Ring captureRelay capture
- · Movement by cursor
- The SD card can be replaced during recording when the sampling interval is 100ms or slower.

When data capturing stops, most recent data is stored in the memory.

Creates data file up to 4GB continously without losing any recording. (Firmware version 2.0 or later: up to 4GB, Firmware version 1.6 or before: 2GB) *In firmware version 2.0 or later, data capacity or capturing time can be set flexibly by users. Specific value (measured value, alarm point) of a particular channel in the recorded data can be searched and found automatically

The cursor can be moved automatically to a specified time in the recorded data.

• Statistical calculation with cursor. The statistical calculation (average, max, min, P-P, effective value) can be determined in between the recorded data specified by the cursor.

Supports measurement and simulation testing using the voltage output module (GL7-DC0)

Allows a simulated testing by outputting the measured data from signals recorded from various input modules and outputs the data through the voltage output module (GL7-DC0).



Outputs the saved data for driving equipment, and the signal of various points are measured simultaneously



Signals that are being captured may not be output at the same time. The output current is max 10mA for each channel. Total output current of the unit is 40mA. If the target object needs to be driven by external power, than a power amplifier may be needed.



Main features

- Easily measure strain gauges using built-in bridge circuit for both 120 and 350 ohm gauges
- Supports excitation power for bridge circuit in constant voltage or current
- Supports TEDS sensors
- Supports a low-pass and anti-aliasing filter
- Enable high-precision measurement in remote sensing and shunt calibration function



Max. 100kS/s

Supported sensors

Strain gauge: 1 gauge in 2-wire, 3-wire, or 4-wire

2 gauges in 3-wire, 4-wire, or 5-wire

4 gauges in 4-wire, or 6-wire

Strain type sensor: 4-wire or 6-wire

Connector for input

D-SUB type connector (standard accessory: 4pcs)

Input cable with NDIS type connector (B-561)



Screw terminal adapter (B-560A)



It can be used without connector cove by using included terminal hold bracket. The terminal holding bracket can be purchased for replacement as option B-560AP.

Extension cable for B-560 / B-560A (B-560-05)

Compensations for High-precision measurement

Remote Sense:

Eliminates the influence from the lead wire resistance

Shunt calibration:

Gain compensation of strain measurement

Charge Module GL7-CHA

Max. 22V

4mA



Main features

- Supports charge and voltage output type sensors
- Now compatible with microphones (Firmware version 2.0 or later)
- Supports TEDS sensors
- Wide variety of filter functions allows high-precision measurements
- Support RMS (effective value) measurement



Charge. IEPE


Max. 100kS/s (10us)

High-precision measurement using various filters

High-precision signal is captured using high-pass, low-pass, and anti-aliasing filter.







Sensors and input connector type

Change or IEPE type sensors can be measured by setting the sensor sensitivity and using the engineering scaling function.

Charge output type sensor Supported acceleration sensor: 0.01pC/(m/s2) to 999.9pC/(m/s2)



Voltage output (IEPE) type sensor

Supported acceleration sensor: 0.01mV/(m/s2) to 999.9mV/(m/s2) Supported microphone sensor: 0.2mV/Pa to 100mV/Pa









Voltage Output Module GL7-DC0

Main features

- Recorded data can be output as an analog voltage, and reproduce the measured anomalies and recorded data (Temperature, humidity, logic/pulse data is excluded.)
- The reference signal for the test created by the GL-Wave Editor (EXCEL macro) can be output into an analog voltage (Signal: Sine wave, pulse wave (any duty ratio), ramp, triangle wave, simple arbitrary waveform, DC.)
- Output voltage: Max. 10V (Output current: Max ±10mA/ch or ±40mA/unit.)

Output 8ch/unit Max. 100kS/s (10µs)

Output terminal and conversion cable





connector

connector






GL-Connection and GL-Wave Editor sloftware are standard accessories.
 GBD is an abbreviation for Graphtec Binary Data.








High Voltage Module GL7-HV

Main features

- High input voltage (Maximum: 1000V)
- Input coupling of DC and AC
- Real-time RMS measurement



Measuring in RMS (effective value)




Volume of data to be rewaveform.




Volume of data recorded becomes small because the sampling speed does not need to be as fast recording sampling spee the RMS value.

DC- or AC-coupling


By using the DC and AC coupling feature, the voltage signal of a small signal superimposed on the input signals or the absolute voltage value can be recorded.





Measures the accumulated value of the DC and AC components. (Absolute voltage of signal.)

It is possible to remove the superimposed DCcompon from the coupled AC signal allowing only the small AC components to be meaured.



High Speed Voltage Module GL7-HSV

Main features

- All isolated input channels (4ch/unit)
- 1MS/s high speed simultaneous sampling
- · Maximum input voltage 100V
- · Supports low-pass filter









Voltage Module GL7-V

Main features

- All isolated input channels (10ch/unit)
- 1kS/s Simultaneous sampling
- Maximum input voltage 100V
- Supports low-pass filter

Voltage 10ch/unit





Voltage/Temperature Module GL7-M

Main features

- All isolated input channels (10ch/unit)
- · Supports multiple input types (4-20mA current loop using 250 ohms shunt)

: max. 50V Voltage

Temperature: Thermocouple and RTD Humidity : optional sensor (B-530)





Supports one humidity sensor per module (B-530).
Additional humidity sensors require an external power supply for the sensors...

Logic/Pulse Module GL7-L/P

Main features

- Switching mode between logic or pulse 16ch/unit
- Logic mode: 1MS/s sampling, Pulse mode: 10kS/s sampling
- Available dedicated cabler

Probe set for Logic input (RIC-10A)

Logic /Pulse Max. 1MS/s 16ch/unit (1µs)

Max. 10kS/s




Attachable number of modules: up to 7 modules using Logic mode, up to 2 modules using Pulse mode. In the Pulse mode, there is a limitation of the sampling speed by the number of channels used.

Reliable measurement with useful functions

External 1/0 (Input/Output) and Alarm output

Output module is used for triggering, external sampling, start/stop, and auto-balance for input and output using the Input/Output cable for GL (B-513 optional). The signals related to the status of alarms are output from the terminal on the alarm output module.



input • Start/Stop control (1ch) • External trigger (1ch) • External sampling (1ch) • Executing auto balance (1ch)

Output Trigger status (1ch)

Alarm output signal specifications

Open collector output

- (pull-up resistance 10KΩ) < Rating of the output element >
- Max. voltage: 50V
- Max. current: 2.0 A
- Max. dissipation: 0.6W

WEB and FTP server for remote control and data transfer / Direct USB connection to the main unit

WEB server

Web browser function allows remote control and remote monitoring of waverform analysis.

FTP server

Data can be transferred between the server and GL7000.

The USB drive mode function enables data to be transferred to the PC from the main module built-in flash memory, SD card memory, or the SSD by drag & drop feature. You can then easily delete the files from the file explorer.

While using the FTP server or the USB drive mode, data files that are being recorded cannot be transferred to the PC.

· WEB, FTP server function


USB drive mode





Backup settings

The GL7000 has a function that periodically backs up recorded data (refer to the chart below). Here, the user can set the conditions for data backup.



Destination	Back	up destin	ation
of data	SD card	SSD	FTP
Built-in flash memory	Yes	Yes	Yes
SD memory card	No	Yes	Yes
een	Voc	Ne	Voc

Backup intervals

Off, 1, 2, 6, 12, 24 hour(s)

Backup destination SD memory card, SSD, FTP. You can not specify the same location as the backup destination and

recording destination.

when the recording format is "CSV", the backup function is not * When Ring recording is set to on, the backup function is not available

NTP client function

The clock on the GL7000 is periodically synchronized with the NTP server.

DHCP client function

The IP address of the GL7000 is automatically obtained from the DHCP server.

Safe recording measures include backing up data on the PC

Application software allows a real time saving of the data while the data is being captured on to the memory of the GL7000.



Storage on GL7000 Transferred data to the PC Captured data is transferred and saved to the PC after the completion of the measurement. During the measurement, free-running mode allows the display of the real time data but not the recording, (Real-time recording is not available using the built-in RAM as the recording destination.)

Captured data is stored to the media and also transferred to the PC simultaneously. Max sampling speed: 1ms/unit when it is saved in the GBD format, 1ms/unit when it is in the CSV format.

Captured data is transferred and saved to the PC after the completion of the measurement. During the measurement, free-running mode allows the display of the real time data but not the recording. (Real-time recording is not available using the built-in RAM as the recording destination.)

Real time recording on the PC can be saved as a CSV file while the data is saved as a GBD file on the main GL7000,
 Maximum sampling speed for this feature is 1ms.

Display options

Allows YT waveform, XY waveform, digital monitoring and FFT measurement (same as the main GL7000 unit)



Customized screens for Data Acquisition Professionals

Various control and setting screens for simplified operation



Setup screen

Recognize the unit to connect to the PC by graphical image on the display.



Setting menu screen

Setting menu on the GL Connection software is similar to the setup screen on the GL7000.

GL-Wave Editor (Excel macro)

Setting menu for the voltage output module Setup for the output function using the GL7-DCO module is set on the GL-Wave Editor (EXCEL macro) with customized data platform for specified measurement.

Multiple window option allows waveforms to be displayed in various forms

* It is required version 2.20

Splits up to 4 windows and each window can display different format (Y-T, XY, FFT, and digits).





Dual windows Ouad windows

When displaying multiple windows, the cursor positions can be synced.

Settings of multiple modules can be displayed simultaneously, and setting conditions can now be saved as CSV data.

Disable saving data to PC*: selection for enabling or disabling data recording on the PC and only to the main unit GL7000.


Remote Lock On/Off Feature*: Setting operation is available on GL7000 under control of GL-Connection.

Useful functions for GL-Connection Software

Supports a user-friendly mouse movement that enables changes in the setting and the related display waveform

Display size of the waveform can be changed using a drag feature on the dotted line with the PC controlled mouse.

The scale of the waveform can be changed using the mouse wheel operation.



The position of the waveform can be shifted up or down using the mouse

Time division can be shifted using the mouse wheel operation.

Optional Features Additional functions for data processing.

The maximum, minimum, peak, and average values are displayed while capturing data. The value between the cursors of the maximum, minimum, peak, average, and RMS will be displayed when replaying selected

File operation:

Data can be converted to CSV file format for a specified time period, or complete data, or multiple files. A file can also be created by compressing or consolidating multiple files.

The search point can be set by the level, alarm, or time (the beginning of the data, center, end, trigger point, the specified time, instruction time, the number specified)

Send mail

Alarm warnings can be sent via Email.

Large-scale channel measurements


Up to 1120 channels can be recorded using the PC platform 10 units of the GL7000 can be connected through 1 PC software using the LAN or the USB hub.

Up to 5 units of the GL7000 can be fully synchronized using the sync. cable

The start/stop trigger, and sampling can be synchronized in the GL7000 when they are connected by a sync cable. The master and slave units are automatically identified. Data is stored in each main unit individually.

Allows connections of Graphtec's midi LOGGER series Maximum channel is up to 2000 when 10 units of GL840 is connected midi LOGGER series

- GL2000, GL980, GL900-4 and GL900-8, GL840, GL820, GL240, GL220
- can all be viewed in real time.



SDK (Software Development Kit) is offered for free Software Development Kit (SDK) is available for real time data transfer and beyond for custom application developed for your need.

• USB driver • Manual (Main unit controls, data communication, data file, etc.) • Sample program (in Visual C++, Visual Basic, .NET framework)

Up to 112ch on one GL7000, Up to 1120ch total

Innut / Output Madula Charifications

todal second	ule Specifications	Voltage	High Speed Voltage			
odel numbe umber of in	er put channels	GL7-V 10 channels	GL7-HSV 4 channels			
put method		All channels isolated unbalanced input,	All channels isolated unbalanced input,			
mplina see	eed (interval)	Simultaneous sampling, Screw terminal (M3 screw 1 k Samples/s to 1 Sample/h (1 ms to 1 hr.)	 simultaneous sampling, BNC connector M Samples/s to 1 Sample/h (1µs to 1 hr.) 			
uilt in RAM		2 million samples for each channel				
easurement easurement	t range t accuracy (*1)	100, 200, 500 mV, 1, 2, 5, 10, 20, 50, 100 V, ar ±0.25% of Full Scale	nd 1-5 V Full Scale			
/D converte	er .	Successive approximation type, 16 bits (effective	ve resolution: 1/40000 of the measuring full rang			
put impeda aximum		1 MΩ ±5% 100 mV to 1 V range: 60 Vp-p,2 V to 100 V ra	nge: INR Vn-n			
put	Between channels ((-) terminals)	60 Vp-p	196.100.19.9			
oltage lay voltage	Between channel/GND Between channels	60 Vp-p 1000 Vp-p (1 minute)				
vithstand)	Between channel/GND	1000 Vp-p (1 minute)				
olation	Between input/GND ide rejection ratio	Min. 50 M0 (at 500 V DC) Min. 90 dB (50/60 Hz, Signal source impedar	nce: May 300 0)			
requency re-	sponse	DC to 1 kHz (+1/-3 dB)	DC to 200 kHz (+1/-3 dB)			
liter	Low pass	Off, Line(1.5 Hz), 5, 50, 500 Hz (at -3 dB, 6dB/oct)	Off, Line(1.5 Hz), 5, 50, 500, 5k. 50k Hz (at -3 dB, 6dB/cot)			
xternal dime	ensions (W×D×H)	Approx. 49 x 136 x 160 mm (Excluding project	tions)			
eight	perature Input Moduli	Approx. 840 g Specifications	Approx. 740 g			
lodel numbe	er	GL7-M				
umber of inp put method	put channels	All channels isolated balanced input. Scans of	hannels for sampling, Screw terminal (M3 scre			
Sampling speed (interval)		100 Samples/s at 10ch to 1 Sample/h (10 ms				
uilt in RAM easurement	Voltage	2 million samples for each channel 20, 50, 100, 200, 500 mV, 1, 2, 5, 10, 20, 50 V	and 1-5 V Full Scale			
ange	Temperature	Thermocouple: K, J, E, T, R, S, B, N, and W (W	(Re5-26)			
		RTD: Pt100, JPt100 (JIS), Pt1000 (IEC751)				
easurement		0 to 100 % RH, using optional humidity senso ±0.1% of Full Scale	TO I SAN DAN DANCE.			
	Temperature Thermocouple	Measurement range	Measurement accuracy			
	R/S	0 ≤ TS ≤ 100°C 100 < TS ≤ 300°C	± 5.2°C ± 3.0°C			
		R: 300 < TS ≤ 1600°C	± (0.05% of reading + 2.0°C)			
	В	S: 300 < TS ≤ 1760°C 400 ≤ TS ≤ 600°C	± (0.05% of reading + 2.0°C) ± 3.5°C			
		600 < TS = 1820°C -200 = TS = -100°C	± (0.05% of reading + 2.0°C)			
	К	-200 s TS s -100°C -100 s TS s 1370°C	± (0.05% of reading + 2.0°C) ± (0.05% of reading + 1.0°C)			
	Ε	-200 ≤ TS ≤ -100°C	± (0.05% of reading + 2.0°C)			
	T	-100 < TS ≤ 800°C	± (0.05% of reading + 1.0°C)			
	1	-200 s TS s -100°C -100 < TS s 400°C	± (0.1% of reading + 1.5°C) ± (0.1% of reading + 0.5°C)			
	J	-200 ± TS ≤ -100°C	± 2.7°C			
		-100 < TS ≤ 100°C 100 < TS ≤ 1100°C	± 1.7°C ± (0.05% of reading + 1.0°C)			
	N	-200 = TS < 0°C 0 = TS = 1300°C	± (0.1% of reading + 1.0°C) ± (0.1% of reading + 1.0°C)			
	W	0 * TS * 1300°C 0 * TS * 2000°C	± (0.1% of reading + 1.0°C)			
		0 * TS. * 2000°C				
	* Wire size of	of thermocouple used is 0.32 mm diameter in	the T type and 0.65 mm diameter in other type			
	RTD Pt100	Measurement range -200 to 850°C (F.S. = 1050°C)	Driving current Accuracy 1 mA ±1.0°C			
	JPt100	-200 to 500°C (F.S. = 700°C)	1 mA ±0.8°C			
J. Compens	Pt1000	-200 to 500°C (F.S. = 700°C) Select internal or external	0.2 mA #0.8°C			
/D converter	T.	Sigma-Delta type, 16 bits (effective resolution	n; 1/40000 of the measuring full range)			
put impedar	nce	1 MΩ ±5%				
put	Between (+)/(-) terminal Between channels ([-) terminals)	60 Vp-p				
oltage	Between channel/GND	60 Vp-p				
ax. voltage vithstand)	Between channels Between channel/GND	350 Vp-p (1 minute) 350 Vp-p (1 minute)				
olation	Between input/GND	Min. 50 MΩ (at 500 V DC)				
	de rejection ratio Moving average	Min. 90 dB (50/60 Hz, Signal source impedar Off, 2, 5, 10, 20, 40	nce: Max. 300 Ω)			
	average.	(Moving average in selected number. When t	he sample is longer than 5 seconds,			
V output		the data sampled in the sub-sample (5 seconds)	nds) will be used for creating the average value			
	ensions (W×D×H)	Driving the humidity (*2) sensor 8-530, 1 cha Approx. 49 x 136 x 160 mm (Excluding project	tions)			
eight	Input Module Specific	Approx. 770 g				
odel numbe		GL7-HV				
umber of ing	put channels	2 channels	hanna a secondar had a description			
put method ampling spe	l red (interval)	All channels isolated unbalanced input, Simu 1 M Samples/s to 1 Sample/h (1 µs to 1 hr.)	itaneous sampling, Isolated BNC connector			
uilt in RAM		2 million samples for each channel				
put coupling easurement	g and measurement DC. AC	AC, DC, AC-RMS, DC-RMS 2, 5, 10, 20, 50, 100, 200, 500, 1000 V Full Sci	ale			
ange	DC-RMS, AC-RMS	1, 2, 5, 10, 20, 50, 100, 200, 500 Vrms Full Sci	ale			
easurement		(Crest Factor: up to 4 in 1 to 200 Vrms range ±0.25% of Full Scale	, up to 2 in 500 Vrms range)			
ccuracy (*4)		Sine wave measurement				
250		±0.5% of Full Scale (at 20 Hz ≤ F ≤ 1 kHz)				
		±1.5% of Full Scale (at 1 kHz < F = 20 kHz) Response time: 500ms (Crest Factor is up to	4)			
	AC-RMS	Sine wave measurement	-			
		±0.5% of Full Scale (at 100 Hz ≤ F ≤ 1 kHz) ±1.5% of Full Scale (at 1 kHz < F ≤ 20 kHz)				
		Response time: 500 ms (Crest Factor is up to 4)				
	r.	Successive Approximation type, 16 bits (effective resolution: 1/40000 of the measuri	ng full range in the DC and AC counling			
/D converter		1/20000 of the measuring full range in the D				
		1 MΩ ±5%	our section of the section of the section of the			
put impeda	nce	1000 \/e = 0				
put impedar aximum [Between (+)/(-) terminal	1000 Vp-p 300 Vrms AC				
put impedar aximum put bitage	Between (+)/(-) terminal Between channels ((-) terminals) Between channel/GND	300 Vrms AC 300 Vrms AC				
put impedar aximum put oltage ax. voltage	Between (*)/(-) terminal Between channels ((-) terminals) Between channels Between channels	300 Vrms AC 300 Vrms AC 2300 Vrms AC (1 minute)				
put Impedal laximum put oltage ax. voltage withstand) olation	Between (+)/(-) terminal between channel/GND Between channel/GND Between channel/GND Between input/GND	300 Yrms AC 300 Yrms AC 2300 Yrms AC (1 minute) 2300 Yrms AC (1 minute) Min. 50 MQ (at 500 V DC)				
put impeda aximum put oltage ax. voltage withstand) olation ommon-mon	Between (+)/(-) terminal Between channels ((-) terminals) Between channel/GND Between channel/GND Between input/GND de rejection ratio	300 Vrms AC 300 Vrms AC 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) Min. 50 MΩ (at 500 V DC) Min. 90 dB (50/40 Hz, Signal source impedar	nce: Max. 300 Ω)			
iput impeda laximum iput oltage ax. voltage withstand) colation ommon-mon	Between (+)/(-) terminal Between channels ((-) terminals) Between channel/GND Between channel/GND Between input/GND de rejection ratio	300 Yrms AC 300 Yrms AC (1 minute) 2300 Yrms AC (1 minute) 2300 Yrms AC (1 minute) Min, 50 Mi (at 500 V DC) Min, 90 dB (50/60 Hz, Signal source impedar DC Coupling; DC to 200 kHz (+17-3 dB)	nce: Max. 300 Ω)			
put oltage lax. voltage withstand) colation ommon-moi requency res	Between (*)/c) terminal Sewen channs () terminal Between channel/GND Between channel/GND Between input/GND Between input/GND de rejection ratio sponse	300 Vrms AC 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) Min. 50 MQ (at 500 V DC) Min. 90 dB (50/60 Hz, Signal source impedar DC Coupling; 0-E to 200 kHz (+1/-3 dB) AC Coupling; 4Hz to 200 kHz (+1/-4.5 dB) DFF, Line (1) SHz, 5, 50, 500, 58, 50k Hz (at	-3 dB, 6dB/oct)			
put impedal aximum put bitage ax. voltage withstand) olation ommon-morequency re-	Between (*)/(-) terminal Beween channels ()) terminals Between channels (BND) Between channels Between channels Between input/GND de rejection ratio sponse	300 Vrms AC 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) Min, 50 MG (45 500 V DC) Min, 90 dB (50/40 Hz, Signal source impedar DC Coupling: DC to 200 kHz (+1/-3 dB) AC Coupling: 4Hz to 200 kHz (+1/-4.5 dB) OFF, Line (1.5 Hz), 50, 50, 50, 55, 50 kz (2 dt Approx. 49 x 136 x 160mm (Excluding project	3 dB, 6dB/oct)			
put impedal aximum put bitage ax. voltage withstand) olation ommon-mon equency re- tternal dime	Between (*)/c) terminal Sewen channs () terminal Between channel/GND Between channel/GND Between input/GND Between input/GND de rejection ratio sponse	300 Vrms AC 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) 2300 Vrms AC (1 minute) Min. 50 MQ (at 500 V DC) Min. 90 dB (50/60 Hz, Signal source impedar DC Coupling; 0-E to 200 kHz (+1/-3 dB) AC Coupling; 4Hz to 200 kHz (+1/-4.5 dB) DFF, Line (1) SHz, 5, 50, 500, 58, 50k Hz (at	-3 dB, 6dB/oct)			

- * Sampling rate is set to 1 second. * GND terminal is connected to ground.

 (*2) Using optional humidity sensor (8-530)

 (*3) Subject to the conditions:

 * Room temperature is 23 ° x 5 ° C. * When 30 minutes or more have elapsed after power was turned on. * Filter is set to 10.

 * Sampling rate is set to 1 second. * GND terminal is connected to ground.

 (*4) Subject to the conditions:

 * Room temperature is 23 ° C * 5 ° C. * When 30 minutes or more have elapsed after power was turned on. * Filter is set to 10.

 * GND terminal is connected to ground. * Measument acroacy of RMS is effective for input voltage of 5 to 100% ineach measurement range.

 (*5) Available ranges vary by the excitation power for the bridge.

 * Nemote sensing is not available when a NDIS connector is used.

 * When a bridge box is used, the connection needs to be 4-wire or 6-wire full bridge.

 When connecting with a Hall bridge (Opposite side), an additional bridge box is required.

 * Bridge excitation: Constant current drives a strain gauge type sensor or a 4-wire full bridge.

 * The shunt calibration is available only when the connection is using a 3-wire, 4-wire quarter bridge, 5-wire full bridge.

 (**) When the built-in resistor 1200 is used for bridge, the available excitation voltage is 1V, 2V, or 2.5V.

 The gauge type and used built-in resistor for bridge can be set by a DIP-SW which is located on the front panel of the module.

 It is required to create the CSV file that is the source for the arbitrary data using the 6t-Wave Editor (Excel macro).

 The Microsoft Excel 2003 (Office 2003) or later.

 (**) Subject to the conditions. * Room temperature is 2.3 ° C * 5 ° C.

 (**) Input prove (RIC-10A) is required to connect signals.

 The measuring mode is set in each module (16 channels).

 In Log mode, up to 7 modules (Up to 32Ch.) can be attached to one main module.

 In Pulse mode, up to 7 modules (Up to 172Ch.) can be attached to one main module.

DC Strain Ion	ut Module Specificatio	ns
Model numb	er	GL7-DCB
Input method	put channels dAll channels isolated	4 channels balanced input, Simultaneous sampling, D-SUB type connector (9 pins, receptacle)
Built in RAM	eed (interval)	100 k Samples/s to 1 Sample/h (10 µs to 1 hr.) 2 million samples for each channel
Input type Neasurement	Strain (*5)	Strain, Voltage, Resistance value (including potentiometer) 500, 1000, 2000, 5000, 10000, 20000 με (με: 10-6 strain)0.2, 0.25, 0.4, 0.5, 1, 2, 2.5, 4, 5, 10 mV/V
range	Voltage Resistance	1, 2, 5, 10, 20, 50, 100, 200, 500 mV, 1, 2, 5 V Full Scale 1, 2, 5, 10, 20, 50, 100, 200, 500 Ω, 1, 2, 5, 10, 20, 50 kΩ Full Scale
Measurement accuracy (*4)	Strain	±(0.2% of Full Scale + 10 με) ±(0.2% of Full Scale + 10 μν)
Contract of the Contract of th	Resistance	±0.5% of Full Scale (More than 1 hour elapsed after power-on)
A/D converte Gauge ratio	DOMESTIC CONTROL OF THE PARTY O	Successive Approximation type, 16 bits (effective resolution: 1/40000 of the measuring full range) 2.0 constant
Supported sensor	Strain (*6)	Strain gauge Quarter bridge (single gauge) in 2-, 3- or 4-wire (supports remote sensing in 3- or 4-wire) Half bridge (dual gauge) in 3-, 4-, 5-wire (supports remote sensing in 4- or 5-wire) Full bridge (quad gauge) in 4- or 6-wire (supports remote sensing in 6-wire) Transducer/Sensor based on a strain gauge
	Resistance	Full bridge type in 4-wire, Full bridge type in 6-wire (supports remote sensing) Resistor, Potentiometer
Bridge resist Built-in elem		50 Ω to 10 kΩ * Available excitation power varies by selection of element. 120 or 350 Ω for the quarter- and half-bridge
Excitation power	Voltage mode	1, 2, 2.5, 5, 10 V DC. * Excitation voltage 5 and 10 V is available when bridge resistance is the 350 0 or higher.
Zero Adjust	Current mode Method	Constant current: 0.1 to 20 mA (supported voltage is up to 10 V.) Fully automatic (via push button or setting the condition menu)
for Strain gauge	Max. Range	±10,000με (με: 10-6 Strain)
Remote sens Shunt Calibra	ition	3- or 4-wire in quarter bridge, 4- or 5-wire in half bridge, 6-wire full bridge Approx. 60 kΩ (120 Ω gauge), Approx. 175 kΩ (350 Ω gauge)
Maximum input	Between (+) / (-) terminal Between channels (i-) terminals)	
voltage Max. voltage	Between channel / GND Between channels	1000 Vp-p (1 minute)
(withstand) Isolation	Between channel / GND Between channel / GND	1000 Vpp (1 minute) Min. 100 MΩ (at 500 V DC)
	de rejection ratio	Min. 80 dB (50/60 Hz, Signal source impedance: Max. 300 Ω) DC to 20 kHz
Filter	Low pass	Off, Line (1.5 Hz), 3, 6, 10, 30, 50, 60, 100, 300, 500 Hz, 1k, 3k, 5k, 10k Hz (in -30dB/oct)
Support	Anti-aliasing Standard	Off, On IEEE 1451.4 Class2 (Temperate No.33)
	Support ensions (W x D x H)	Reading information from the sensor and setting it to module Approx. 49 x 136 x 160mm (Excluding Protection)
Weight Charge Input		Approx. 840 g
Model numb		GL7-CHA 4 channels
Input metho		All channels isolated unbalanced input, Simultaneous sampling,
	eed (interval)	BNC and Miniature connector (#10-32UNF) 100 k Samples/s to 1 sample/h (10 µs to 1 hr.)
Built in RAM Input type		2 million samples for each channel Sensor in charge output type, Sensor in IEPE type, Voltage, Microphone(*8)
Input couplir	ng	Sensor: Charge-RMS, IEPE-RMS Voltage: DC, AC, DC-RMS, AC-RMS
Measurement range	Acceleration sensor input Microphone(*8)	1, 2, 5, 10, 20, 50, 100, 200, 500, 1000, 2000, 5000, 10000, 20000, 50000 m/s² 200, 400, 500mPa, 1, 2, 4, 5, 10, 20, 40, 50, 100, 400, 500Pa
inige	Voltage input	DC, AC coupling: 50, 100, 200, 500 mV, 1, 2, 5, 10 V
		RMS measurement: 20, 50, 100, 200, 500 mVrms, 1, 2, 5 Vrms (Crest Factor in RMS measurement: up to 4 in 20 mVrms to 2 Vrms range, up to 2 in 5 Vrms range)
Supported sensor	Charge output type	0.01 pC/(m/s²) to 999.9 pC/(m/s²) Effective range of measurement range varies depending on sensor sensitivity.
sensitivity	IEPE type	0.01 mV/(m/s²) to 999.9 mV/(m/s²) Effective range of measurement range varies depending on sensor sensitivity.
Measurement	Microphone(*8) Charge output type	D.2mV/Pa to 100mV/Pa ±0.9% of Full Scale ([sensor sensitivity] × [setting range] ≥ 20 pC)
accuracy (*4)	IEPE type	±0.25% of Full Scale ([sensor sensitivity] × [setting range] × 200 mV)
A/D converte Input impeda	ance	Successive approximation type, 16 bits [effective resolution; $1/40000$ of the measuring full range) $100 \text{ k}\Omega \pm 5\%$
Excitation po Maximum in	out charge signal	4 or 8 mA (supported voltage: 22 V ±10%) Max. 50000 pC
Maximum input	Between (+) / (-) terminal Between channels (-) terminals	25 Vp-p 25 Vp-p
voltage Max. voltage	Between channel / GND Between channels	25 Vp-p 300 Vp-p (1 minute)
(withstand) Isolation	Between channel / GND	300 Vp-p (1 minute)
Common-mo	Between input / GND ode rejection ratio	Min. 50 MΩ (at 500 V DC) Min. 80 dB (50/60 Hz, Signal source impedance; Max. 300 Ω)
Frequency response	Charge type IEPE type	1.5 Hz to 45 kHz 1 Hz to 45 kHz
Filter	Hi pass Low pass	Off, 0.15, 1, 10 Hz (It depends on input conditions.) Off, Line (1.5 Hz), 3, 6, 10, 30, 50, 60, 100, 300, 500 Hz, 1k, 3k, 5k, 10k Hz (in -30dB/oct)
Support	Anti-aliasing Standard	Off, Line (1.5 Hz), 3, 6, 10, 30, 50, 60, 100, 300, 500 Hz, 1k, 3k, 5k, 10k Hz (in -30dB/oct) Off, On IEEE 1451.4 Class1 (Temperate No.25 for sensor, Temperate No.27 for microphone)
TEDS Calculation fi	Support	Reading information from the sensor and setting it to module Integration (convert measurement to velocity),
		Double Integration (convert measurement to displacement)
Weight	ensions (W x D x H)	Approx. 49 x 136 x 160mm (Excluding projections) Approx. 850 g
Voltage Outp Model numb	out Module Specification	GL7-DC0
Number of o Output meth	utput channels od	8 channels All channels common ground, SMA (Sub-miniature version A) connector
	eed (interval) Source of data	Up to 100 k Samples/s (10 µs) Measurement data, Edited measurement data, Generated arbitrary data(*9),
condition	Source of	Generated simple waveform (DC voltage and sine, triangle, ramp, pulse waveform) Module of Voltage (GL7-V), Voltage/Temperature (GL7-M), High speed voltage (GL7-HSV),
	measurement data	High voltage (GL7-HV), DC strain (GL7-DCB), and Charge (GL7-CHA)
	Output condition	Signal can be measured by the input module even while the signal is output from the DCO module. Measurement data except the temperature, humidity and logic/pulse are able to output.
Output range	Voltage Current	± 1, 2, 5, 10 V Full Scale Up to ± 10 mA in each channel (total output current of unit is up to 40 mA.)
Output impe		Max. 1 0 ±0.25% of Full Scale
D/A converte Filter	Low pass	Resolution 16 bits (effective resolution; 1/20000 of the output full range) OFF, Line(1,5 Hz), 5, 50, 500, 5k, 50k Hz
	NO STATE OF THE PARTY OF THE PA	* This filter is the smoothing filter to remove the noise on output of the D/A converter.
Weight	ensions (W x D x H)	Approx. 49 x 136 x 160mm (Excluding projections) Approx. 770g
Model numb	input Module specifica er	GL7-L/P
Number of in Input methor	put channels	16 channels All channels common ground, Simultaneous sampling, Circular connector (4ch/connector)(*11)
Sampling	Logic mode Pulse mode	10 k Samples/s to 1 Sample/h (100 µs to 1 hr.)
Built-in RAM		2 million samples for each channels
Measuremen Pulse input n	node	Logic input mode or Pulse input mode (*12) Rotation count (RPM), Accumulating count, Instant count
Rotation count (RPM)	Function	Counting the number of pulses per sampling interval and then it is converted to RPM 50, 500, 5000, 50 k, 500 k, 5 M, 50 M, 50 M rpm Full Scale
Accumulating count		Accumulating the number of pulses from the start of measurement 50, 500, 5000, 50 k, 500 k, 5 M, 50 M, 50 M counts Full Scale
Instant	Function	Counting the number of pulses per sampling interval (count is reset at each sampling)
count Maximum nu	Span mber of count	50, 500, 5000, 50 k, 500 k, 5 M, 50 M, 500 M counts Full Scale 15 M counts (24 bits counter is used)
input signal	Voltage range Signal type	0 to 24 V (common ground) Contact (Relay), Open collector, Voltage
nove views		Approx. 2.5 V
z Westerffren	Threshold Hysteresis	Approx. 0.5 V (2.5 V to 3 V)
Filter	Hysteresis ensions (W×D×H)	Approx. 0.5 V (2.5 V to 3 V) Off or 0n (-3 dB at 50 Hz) Approx. 49 x 138 x 160 mm (Excluding projections)

GL7000 specifi	ications	
Item		Description
Number of mo		Attached to up to 10 modules (*1), Max. 112 channels in 1 of GL7000
External Input/ Output	input	Start/Stop, External trigger, External sampling, Auto balance (*3) Signal type: Contact (relay), Open collector, Voltage
signals (*2)	Output	Trigger, Busy (*3), Alarm (10 channels) (*4)
signato (E)	Coupor	Signal type: Open collector (pulled-up by resistor 10 kΩ)
Trigger,	Trigger action	Start or Stop capturing data by the trigger
Alarm	Trigger repeat	Enabled (ON): Automatically re-armed for the next data capture function
function		Disabled (OFF): Data capture is completed in a single trigger
	Tringer courses	(Hold off repeat action in specified period: Previous start to next start, previous stop to next start)
	Trigger source	Start: Off, Measured signal, Alarm, External signal, Clock, Week or Time Stop: Off, Measured signal, Alarm, External signal, Clock, Week or Time
	Trigger determination	Combination: OR or AND condition at the level of signal or edge of signal
	conditions for	Analog: Higher/Rising, Lower/Falling, Window-in, Window-out
	measured signal	Logic (*5): Higher/Rising, Lower/Falling
	HILL SALES CONTROL OF THE PARTY	Pulse (*5): Higher/Rising, Lower/Falling, Window-in, Window-out
	Alarm	Combination: OR or AND condition at the level of signal or edge of signal
	determination condition (*6)	Analog: Higher/Rising, Lower/Falling, Window-in, Window-out Logic (*5): Higher/Rising, Lower/Falling
	continuit ('0)	Pulse (*5): Higher/Rising, Lower/Falling, Window-in, Window-out
	Alarm output	10 channels
	Pre-trigger (*7)	Number of data before trigger. Up to specified number of captured data
Calculation	Between channels	Addition, Subtraction, Multiplication and Division for two analog inputs
function		(Sampling speed is limited up to 10 Samples/s (100 ms interval).
	Statistical	Available arithmetic element and the output destination is the analog input channel 1 to 100.) Select two calculations from Average, Peak, Max., Min. in real time and replay (*8)
Move function	of the display range	Beginning, center or end of the data, Trigger point, Specific time (absolute, relative), Call curso
Search function		Search for analog signal levels, logic signal pattern, pulse signal levels or alarm point in captured data
Annotation fun	ction	Comment can be set in each channel (up to 31 alphanumeric characters)
Message / Mai	ker functions	Message: The registered messages or entered message is able to be recorded for any timing
		Up to 8 messages can be pre-registered.
Docume		Marker: Marker is able to record for occurring alarm or power failure.
Resume		Resume automatically in the same condition after power is recovered
FFT analysis	Analyzing frequency range	as when the power failure occurred during data capture (*9)
function	Number of points	0.08, 0.2, 0.4, 0.8, 1.6, 2, 3.2, 4, 8, 20, 40, 80, 200, 400, 800 Hz, 2, 4, 8, 20, 40, 80, 200, 400 kHz, 500, 1000, 2000, 4000, 10000
(Firmware ver.	Window function	Rectangular, Hanning, Hamming, Blackman, Flat-top, Exponential
1.20 or later)	Averaging	Summation average, Exponential average, Peak hold
	Channels	4 channels
	Functions	Y-T, Linear, Power, PSD, Cross, Transfer function, Coherence, COP
Interface to PC	Display mode	Single display, Dual display, Nyquist Ethernet (10 BASE-T/100 BASE-TX), USB 2.0 (High speed)
Network functi	on	WEB server, FTP server, FTP client, NTP client, DHCP client
USB drive mod		Emulate the USB memory device (*10)
Storage	Built-in	RAM (2 million samples, built-in amplifier module), Flash memory (4 GB, built-in the main module) [*1]]
device	External (*12)	SD card (Support SDHC, up to 32GB) slot, SSD (Approx. 128GB (*11))
		The file for capturing data is limited up to 4GB. (*13) 1 MS/S(1 million samples per second) to 1S/h (1 sample per hour), and synchronized with external sampling signal
Data saving	Sampling speed	1 MS/S(1 million samples per second) to 15/h (1 sample per hour), and synchronized with external sampling signal
function	(Interval)	(Interval: 1, 2, 5, 10, 20, 50, 100, 200, 500 µs, 1, 2, 5, 10, 20, 50, 100, 200, 500 ms,
		 2, 5, 10, 20, 30, 1, 2, 5, 10, 20, 30 min, 1 hur) The maximum sapling speed (minimum sampling interval) is different depending on the type of module.
		* 5ampling can be set up to the fastest speed among multiple type connected modules.
		* The maximum sampling speed (minimum sampling interval) varies depending on the specified recording destination.
		Built-in RAM: up to 1 MS/s (1 µs interval)
		SSD module: up to 500 kS/s (2 µs interval) at 1 or 2 modules installed, up to 200 kS/s (5 µs interval)
		at 3 or 4 modules installed, up to 1 kS/s (1 ms interval) at 5 or 10 modules installed
		Built-in Flash memory: up to 1 MS/s (1 µs interval)
	Captured data (*12)	External SD Flash memory: up to 1 kS/s (1 ms interval) Built-in RAM, Built-in Flash, SD memory card, SSD (Data is saved directly to it.)
	Data in built-in RAM	Specified number of data up 2 million samples in increments of 1
	Auto save (*12)	Available for the built-in RAM
		Enabled (ON): Data in the RAM is saved automatically to the built-in Flash, SD memory card, SSD
		Disabled (OFF): Data in the RAM is not maintained after power is turned off
	Capturing mode (*12)	Mode: Off, Normal, Ring, Relay
		Ring (*14): Saved most recent data (Number of capturing data: 1000 to 2000000 points,
		Destination of data: Built-in RAM, Built-in Flash, SD memory card, SSD)
		Relay (*13,*15): Saved data to multiple file without losing data until capturing data is stopped (Destination of data: Built-in Flash, 5D memory card, SSD)
	During data capture (*17)	Displaying information in two windows, Hot-swapping the SD memory card, Saving data in between cursors
	Backup (*12)	Backup interval: Off, 1, 2, 6, 12, 24 hrs.
	Assessment of the second	Data destination: SD memory card, SSD, FTP server
		Data destination for backup cannot be specified to the same storage for destination of capturing data.
	Dual	It enables to record signal with two sampling speed. While the signal is recorded with low speed sampling
	sampling function (*18)	for long term recording, the transient part is recorded with high speed sampling after the trigger occurs
	torscount to)	Carrent (Low-speed) Recording media : Built-in flash memory or SD card
		Sampling Interval : 1, 2, 5, 10, 20, 50, 100, 125, 200, 250, 500ms, 1, 2, 5, 10, 20, 30s, 1, 2, 5, 10, 20, 30min, 1h
		Trigger timer feature: Starting time, Stopping time, Repeat recording
		Event (High-speed)
		Recording media: Built-in RAM or SSD (optional)
		Sampling interval : 1, 2, 5, 10, 20, 50, 100, 200, 500µs
Engineering so	ate function	Measured value can be converted to the engineering unit
		Analog voltage: Converts by four reference points (gain, offset) Temperature: Converts by two reference points (offset)
		Pulse count: Converts by two reference points (gain)
Synchronizatio	n between units	Start and Trioger (*16)
Operating envi		Start and Trigger (*16) D to 40°C, 5 to 85% RH (non condensed)
Power source		100 to 240 V AC, 50 to 60Hz
Power consum		110VA
		Quick guide, CD-ROM, AC power cable
Standard acces		
Standard acces	isions (W x D x H)	Main module: Approx. 193 x 141 x 160 mm (Excluding Projection),
Standard acce: External dimer		Main module: Approx. 193 x 141 x 160 mm (Excluding Projection), Alarm output terminal: Approx. 30 x 136 x 145 mm (Excluding projection)
Standard acce External dimer Weight	isions (W x D x H)	Main module: Approx. 193 x 141 x 160 mm (Excluding Projection),

Fixed modules: Approx. 22 kg, Alaim output terminal: Approx. 350 g

Excluding the function module as the Display module or 550 module. In case of the DC Strain module (GL7-DCB): up to 8 modules
in case of the Logic/Pulse module (GL7-L/P): input mode is selected in the logic or pulse for each module, up to 7 modules when
the module is used in the logic mode, up to 2 modules when the module is used in the pulse mode.
The Input/Output cable (B-513) is required for connecting the signal. The Auto balance signal input and the Busy signal
output are available in the DC Strain module (GL7-DCB).
It is available on the DC strain module (GL7-DCB).
It is available on the DC strain module (GL7-DCB).
It is available on the Logic/Pulse (GL7-L/P) module.
Method of detection
Voll./Temp. module:
The alarm is detected in the sampling interval when the sampling interval is shorter than 5 seconds and reported.
The alarm is detected in the sampling interval when the sampling interval is shorter than 5 seconds and reported.

Other modules. (+1)

Voll./Temp. module:
The alarm is detected every 5 seconds when the sampling interval is longer than 5 seconds and reported.
The alarm is detected in the sampling interval when the sampling interval is shorter than 5 seconds and reported.
Other modules:
The alarm is detected every 1 ms when the sampling interval is shorter than 1 ms. The alarm is detected in the sampling interval is solven the sampling interval is set between 2 ms to 5 seconds and reported. The alarm is detected in the sampling interval is longer than 5 seconds and reported.
The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The pre-trigger function may not available in combination with the trigger settings.

The sest of real time calculation is displayed in the digital display mode.
Available sampling speed is the 10 samples/s (100 ms interval).

The LSB drive mode is started by setting of the switch on the main module. It is can be also started when the power is turned on while pressing the START/STDP key on the display module.

The SD memory card is not included as a standard accessory. Compatible SD card type: SD, SDHC Speed class 4 or faster.

The SD memory card is not included as a standard accessory. Compatible SD card type: SD, SDHC Speed class 4 or faster.

The File for recording data is limited up to 468 not firmware version 2.0 or later, 268 on limitware version 1.6 or before.

The capacity for saving the data is set to one third of available memory when the captured data destination is set to a device other than the built-in-RAM. Available sampling speed in limited up to 100 sa

Supported OS Functions Controlled unit		Windows 10 / 8.1	/ 8/ 7 (32/64-bit edition)			
Controlled unit		Control GL7000,	Real-time data capture, Replay data, Data format conversion th GL7000, GL2000, GL980, GL900, GL840, GL820, GL240, GL220			
		Up to 10 units with GL7000, GL2000, GL980, GL900, GL840, GL820, GL240, GL220 GL7000 only: max. 1120 channels				
		Mission with GL st	X. HZU Channels			
GL7000 Setting	ns control	Mixing with GL series: max. 2000 channels Input settings, Memory settings, Trigger and Alarm settings, Other settings				
Captured data	(*19)	" BUIL-IN RAM (B	inary format), Built-in Flash memory (Binary, C5V format),			
	No.	SD memory card (Binary, CSV format), SSD (Binary, CSV format) The sampling speed is limited by the number of channels used when data is saved in the CSV format.				
		(1 ms per channel, When 10 channels are set, sampling is limited to 10 ms.)				
Brooks and to be		* When captured o	lata is saved to the built-in RAM or SSD, data cannot be saved on the PC in real time. n, Logic waveform, Pulse waveform, Digital values			
Displayed infor	rmation	Analog waveform	1, Logic waveform, Pulse waveform, Digital Values			
Display mode		Y-T waveform with digital values, XY graph in real time/replay saved data (ver. 1.20 or later), FFT measurement (ver. 1.20 or later), Cursor information, Capture condition, Alarm information				
		Measuring condi	tion setting list (*20)			
		Content: channel r	number, line color, annotation, input type, measuring range, filter, unit, span, scaling			
		Function: Output in CSV format, Link to detailed setting Converts binary data to the CSV data (specific period, all data in one file, multiple files),				
File operation						
		Creates a new file	e with compression or by consolidating multiple files.			
Warning Funct Statistical calcu		Send e-mail to th	ie specified address when the alarms occur faximum, Minimum, Peak or Average			
Statistical calci	utation	Capturing data: N	faximum, Minimum, Peak or Average faximum, Minimum, Peak Average or PMS in between currents			
Search function		Replaying data: Maximum, Minimum, Peak, Average or RMS in between cursors Search specified signal level point, alarm point, and time				
Fursor synchri	onization (*20)	Synchronizing cu	rsor position on multiple screens displaying different data file			
	The state of the s	From the beginn	ing: Synchronize the cursor position from the beginning of each screen			
		Position from pre	sent: Synchronize from the current cursor position of each screen			
	te lock of GL7000 (*20)	It allows to make sett	ing operation using control panel on GL7000 even when GL7000 is under the control of software.			
Operation lock		Operation screen	can be locked (It is unlocked with a password.)			
FFT analysis	Analyzing frequency range	0.08, 0.2, 0.4, 0.8	, 1.6, 2, 3.2, 4, 8, 20, 40, 80, 200, 400, 800 Hz, 2, 4, 8, 20, 40, 80, 200, 400 kHz 4000, 10000			
function	Number of points					
(Firmware ver.	Window function	Rectangular, Han	ning, Hamming, Blackman, Flat-top, Exponential			
1.20 or later)	Averaging Channels	4 channels	age, Exponential average, Peak hold			
	Functions		er, PSD, Cross, Transfer function, Coherence, COP			
	Display mode	Single display, D.	ual display. Nyquist			
Data recording dest	tination selection (*20)	Selecting to reco	rd data to GL7000 only or PC together with GL7000			
Creating outpu	it data function	Saved data file (0	SBD/CSV format) in the PC, Saved data file (GBD format) in the GL7000,			
(Version 1.40 o	or later)	Generated simple	e waveform (DC voltage and sine, triangle, ramp, pulse waveform)			
		* This function is a	vailable when the analog voltage output module (GL7-DC0) is attached to the GL7000			
	e GL7-DISP (option)	The signal is out	put from the GL7-DCO module.			
Model number	e GEZ-DISP (Option)	GL7-DISP				
Display device		5.7-inch TFT color LCD monitor (VGA: 640 x 480 dots) Touch panel and Cursor keys (*21)				
Operation		Touch panel and Cursor keys (*21)				
Displayed lang	vage	English, French, German, Chinese, Korean, Japanese				
Screen saver		Turns off back-lik	aht by 10, 30 sec., 1, 2, 5, 10, 30, 60 min.			
Displayed Infor	rmation	Waveform in Y-T with digital values, Waveform only, Digital value, Waveform in XY				
Connection cal		LAN cable (CAT5 class, Straight connection, Up to 10 m) (*22)				
Standard acces	nsions (W x D x H)	Approx 197 × 36	ed mount, Connection cable (40 cm). Ground cable, Screws .5 x 119 mm (Excluding projection)			
Weight	ISIOIIS (W V D V II)	Approx. 530 g	3 x 117 mm (excluding projection)			
	.7-SSD (option) spec	cification				
SSD module GI	The second secon	GL7-SSD				
SSD module GI	Storage device					
SSD module GI Model number Storage device	8	Solid state disk (SSD)			
Model number Storage device Capacity (*23)	t and the same	Solid state disk (Approx. 128GB (T	he file size of the recorded data is limited up to 468.)			
SSD module G Model number Storage device Capacity (*23) Sampling	Attached to	Solid state disk (he file size of the recorded data is limited up to 468.)			
SSD module G Model number Storage device Capacity (*23) Sampling speed	Attached to 1 or 2 modules	Solid state disk (Approx, 128GB (T Max. 1 M Sample.	he file size of the recorded data is limited up to 4GB.) /s (1 μs)			
SSD module G Model number Storage device Capacity (*23) Sampling	Attached to 1 or 2 modules Attached to	Solid state disk (Approx. 128GB (T	he file size of the recorded data is limited up to 4GB.) /s (1 μs)			
SSD module G Model number Storage device Capacity (*23) Sampling speed	Attached to 1 or 2 modules Attached to 3 or 4 modules	Solid state disk (: Approx, 128GB (I Max. 1 M Sample, Max. 500 k Samp	he file size of the recorded data is limited up to 468.) /s (1 µs) lle/s (2 µs)			
SSD module G Model number Storage device Capacity (*23) Sampling speed	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to	Solid state disk (Approx, 128GB (T Max. 1 M Sample.	he file size of the recorded data is limited up to 468.) /s (1 µs) le/s (2 µs)			
SSD module G Model number Storage devices Capacity (*23) Sampling speed (*24)(*25)	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules	Solid state disk (: Approx. 128GB (1 Max. 1 M Sample: Max. 500 k Samp Max. 200 k Samp	he file size of the recorded data is limited up to 468.) /s (1 μs) lide/s (2 μs)			
SSD module 61 Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules assions (W x D x H)	Solid state disk (: Approx. 128GB (1 Max. 1 M Sample: Max. 500 k Samp Max. 200 k Samp	he file size of the recorded data is limited up to 468.) /s (1 µs) le/s (2 µs)			
SSD module Gl Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and ad	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules	Solid state disk (: Approx. 128GB (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g	he file size of the recorded data is limited up to 468.) //s (1 μs) le/s (2 μs) le/s (5 μs) x 180 mm (Excluding projection)			
SSD module Gl Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and an	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules assions (W x D x H)	Solid state disk (Approx. 12868 (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number	he file size of the recorded data is limited up to 468.) /5 (1 μs) sle/s (2 μs) sle/s (5 μs) x 180 mm (Excluding projection) [Remarks			
S50 module 6i Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and an Item Sync. Cable	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules assions (W x D x H)	Solid state disk (Approx. 1286B (I Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559	he file size of the recorded data is limited up to 468.) //s (1 μs) lie/s (2 μs) lie/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000			
SSD module 6i Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dirner Weight Options and an Item Sync. Cable Carrying tool	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules assions (W x D x H)	Solid state disk (Approx. 128G8 (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585	he file size of the recorded data is limited up to 468.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached.			
S50 module 6i Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and an Item Sync, Cable	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules assions (W x D x H)	Solid state disk (Approx. 1286B (I Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559	he file size of the recorded data is limited up to 468.) //s (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks I m long, Synchronizing between GL7000 Can carry 6L7000 with up to 3 modules attached. Can store 6L7000 with up to 3 modules.			
SSD module 6/ Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Diptions and ad Item Sync, Cable Carrying tool Storage case	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W x D x H)	Solid state disk (Approx. 12868 (1 Approx. 12868 (1) Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Modet number B-589 B-585 B-586	he file size of the recorded data is limited up to 46B.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The raster can work only on smooth surface.			
SSD module 6/ Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and at tem. Cable Carrying tool Storage case Input cable, Sa	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W x D x H) ccessories	Solid state disk (Approx. 128G8 (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585	he file size of the recorded data is limited up to 468.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry 6L7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated 1.2 m long 300 VD. C. CAT III.			
SSD module 6/ Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and at tem. Cable Carrying tool Storage case Input cable, Sa	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W x D x H) ccessories	Solid state disk C Approx. 12868 (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Modet number B-589 B-588 RiC-10A RiC-10A RiC-104	he file size of the recorded data is limited up to 468.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry 6L7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated 1.2 m long 300 VD. C. CAT III.			
SSD module of Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and an Item Sync. Cable Carrying tool Storage case Probe set for Linguit cable, 8 Input	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W × D × H) ccessories ogic input tile probe - BNC KC - BNC mana - BNC	Solid state disk C Approx. 1286 (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-10A RIC-142 RIC-143	he file size of the recorded data is limited up to 468.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry 6L7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated 1.2 m long 300 VD. C. CAT III.			
SSD module & Model number Storage device Capacity (*23) Sampling speed (*24)(*25). External dimer Weight (*25). External dimer Weight (*25). External dimer Weight (*26). External dim	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisons (W x D x H) coastories cogic input file probe - BNC CC - BNC cnana - BNC mana - BNC	Solid state disk C Approx. 1286B (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RiC-10A RiC-101A RiC-143 RiC-143 RiC-143	he file size of the recorded data is limited up to 468.) /s (1 µs) lide/s (2 µs) lide/s (5 µs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Poise module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated, 1.2 m long, 300 v DC, CAT II Insulated, 1.5 m long, 1000 v DC, CAT II Insulated, 1.6 m long, 300 v DC, CAT II Insulated, 1.6 m long, 300 v DC, CAT II Insulated, 1.6 m long, 300 v DC, CAT II Insulated, 1.6 m long, 300 v DC, CAT II Insulated, 1.6 m long, 1000 v DC, CAT II Insulated, 1.6 m long, 1000 v DC, CAT II Insulated, 1.6 m long, 1000 v DC, CAT II			
\$50 modulo G Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer weight personal dimer weight personal speed (*24)(*25) External dimer weight personal speed (*24)(*25) External dimer weight personal speed (*24)(*25) External dimer weight litem \$50 mod and titem \$50 mo	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W × D × H) ccessories ogic input tile probe - BNC KC - BNC mana - BNC mana - BNC mana - BNC manal selections	Solid state disk C Approx. 1286 ft Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-10A RIC-142 RIC-142 RIC-143 RIC-147 RIC-147	he file size of the recorded data is limited up to 468.) /5 (1 µs) lie/s (2 µs) lie/s (5 µs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated, 1,5 m long, 1000 V DC, CAT II Insulated, 1,6 m long, 6000 V DC, CAT II Insulated, 1,6 m long, 1000 V DC, CAT II			
\$50 modulo G Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer weight personal dimer weight personal speed (*24)(*25) External dimer weight personal speed (*24)(*25) External dimer weight personal speed (*24)(*25) External dimer weight litem \$50 mod and titem \$50 mo	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W × D × H) ccessories ogic input tile probe - BNC KC - BNC mana - BNC mana - BNC mana - BNC manal selections	Solid state disk C Approx. 1286 ft Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-10A RIC-142 RIC-142 RIC-143 RIC-147 RIC-147	he file size of the recorded data is limited up to 468.) /5 (1 µs) lie/s (2 µs) lie/s (5 µs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated, 1,5 m long, 1000 V DC, CAT II Insulated, 1,6 m long, 6000 V DC, CAT II Insulated, 1,6 m long, 1000 V DC, CAT II			
\$50 modulo 6 Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Leading Speed (*24)(*25) External dimer Weight Leading Speed (*24)(*25) External dimer Weight Leading Speed (*24)(*25) External dimer Leading	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 30 modules stions (W x D x H) cessories ogic input the probe - BNC IC - BNC Inana - BNC Inana - BNC Inana - BNC Inana - BNC Indide size) (*26) middle size) (*26)	Solid state disk C Approx. 1286 ft Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-141A RIC-141A RIC-141A RIC-141A RIC-141A RIC-141A RIC-141A RIC-141A RIC-141A	he file size of the recorded data is limited up to 468.) /s (µs) //s (µs) //s (µs) //s (ps) /			
\$550 modulo G Model number Storage device Capacity (*23) sampling speed (*24)(*25) External direct Weight politics and air telm system of the Carrying tool Storage case Propost cable, Salinput cable, Salinp	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 10 modules sisions (W x D x H) ccessories cogic input tie probe – BNC CC – BNC mana – BNC mana – BNC small size) (*26) middle size) (*26) *26)	Solid state disk C Approx. 1286B (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-599 B-585 B-585 RIC-10A RIC-141A RIC-143 RIC-143 RIC-144A RIC-1445 RIC-145 RIC-146 RIC-146	he file size of the recorded data is limited up to 468.) /5 (1 μs) lide/s (2 μs) lide/s (5 μs) ke/s (5 μs) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip. Insulated, 1.5 m long, 1000 V DC, CAT II. Insulated, 1.5 m long, 1000 V DC, CAT III. For RIC-143, Aperture 11 mm, 300 V DC, CAT III. For RIC-143/RIC-147, Aperture 20 mm, 1000 V DC, CAT III, Max. 15 A For RIC-143/RIC-147, Aperture 20 mm, 1000 V DC, CAT III, Max. 1 A 2 m long, Bare wire for signal connection - Connector for GL series			
\$50 modulo G Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dirner Weight External dirner Weight Sync, Cable Carrying tool Storage case Probe set for Linput cable, Salnput cable, Salnpu	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules Attached to 6 to 2 modules Attached to 7 to 2 modules Attached to 7 to 2 modules Attached to 7 to 2 modules Attached to 8 to 2 modules Attached to 2 modules Atta	Solid state disk C Approx. 1286 B (1 Max. 1 M Sample. Max. 200 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-101A RIC-142 RIC-143 RIC-143 RIC-145 RIC-145 RIC-145 RIC-146 B-513	he file size of the recorded data is limited up to 468.) /s (1 µs) lie/s (2 µs) lie/s (5 µs) lie/s (5 µs) X 180 mm (Excluding projection) Remarks I m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Puise module (60.7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated, 1.5 m long, 300 v DC, CAT II Insulated, 1.6 m long, 600 v DC, CAT II Insulated, 1.6 m long, 600 v DC, CAT II Insulated, 1.6 m long, 600 v DC, CAT II For RIC-143/RIC-147, Aperture 2 D mm, 1000 v DC, CAT II, Max. 15 A For RIC-143/RIC-147, Aperture 5 mm, 1000 v DC, CAT II, Max. 15 A I m cables for signal connection - Connector for GL series 3 m cables for signal connection - Connector for GL series 3 m cables for signal connection - Connector for GL series			
SSD module & Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Options and an Item Sync. Cable Carrying tool Storage case Probe set for Liput cable, Balinput cable	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 or 8 modules Attached to 5 to 10 modules Attached to 5 to 10 modules asions (W x D x H) ccessories ogic input tle probe - BNC CC - BNC innana - BNC small size) (*26) middle size (*26) *26) able for GL or (*27) CC CC	Solid state disk C Approx. 12868 (1 Max. 1 M Sample. Max. 200 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 RIC-104 RIC-142 RIC-142 RIC-144 RIC-143 RIC-144 RIC-145 RIC-146 B-513 B-530 B-530	he file size of the recorded data is limited up to 468.) /5 (1 µs) lie/s (2 µs) lie/s (5 µs) /* (1 µs) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Puße module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip. Insulated, 1.2 m long, 300 v DC, CAT II. Insulated, 1.5 m long, 1000 v DC, CAT III. Insulated, 1.6 m long, 1000 v DC, CAT III. Max. 15 A. For RIC-143, Aperture 11 mm, 300 v DC, CAT III. Max. 15 A. For RIC-143/RIC-147, Aperture 20 mm, 1000 v DC, CAT III, Max. 1.4 Z m long, Bare wire for signal connection - Connector for GL series 3 m cables for signal and power			
\$50 modulo G Model number Storage device Capacity (*23) sampling speed (*24)(*25) External dirner weight carrying tool carrying tool Storage case Proput cable, 8h Input cable, 8a Input cab	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 10 modules Attached to 6 to 2 modules Attached to 7 to 2 modules Attached to 7 to 2 modules Attached to 7 to 2 modules Attached to 8 to 2 modules Attached to 2 modules Atta	Solid state disk C Approx. 1286 B (1 Max. 1 M Sample. Max. 200 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-586 RIC-101A RIC-142 RIC-143 RIC-143 RIC-145 RIC-145 RIC-145 RIC-146 B-513	the file size of the recorded data is limited up to 46B.) /5 (1 µs) lie/s (2 µs) lie/s (5 µs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Pulse module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip. Insulated, 1.5 m long, 300 v DC, CAT II. Insulated, 1.6 m long, 600 v DC, CAT III. Insulated, 1.6 m long, 600 v DC, CAT III. Insulated, 1.6 m long, 600 v DC, CAT III. Insulated, 1.6 m long, 600 v DC, CAT III. The Carl Carl Carl Carl Carl Carl Carl Carl			
\$50 modulo G Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight External dimer Weight Sync. Cable Carrying tool Storage case Probe set for Linput cable, 53 input cable, 58 input cabl	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 5 to 30 modules Attached to 6 to 9 modules Attached to 6 to 9 modules 6 modules 6 modules 6 modules 6 modules 7 modules	Solid state disk C Approx. 1286 B (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Modet number B-589 B-588 B-588 RIC-101A RIC-101A RIC-104	he file size of the recorded data is limited up to 468.) /s (µs) //s (µs) //s (µs) //s (ys) //s (ys)			
\$50 modulo G Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dimer Weight Epitons and an Item Synn, Cable Carrying tool Storage case Probe set for Linguit cable, 86 input cable, 88 input cable, 80 input cable	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 30 modules sisons (W x D x H) Cossories Ogic input le probe - BNC (C - BNC mana - BNC cossories Ogic input le probe - BNC (C - BNC mana - BNC	Solid state disk C Approx. 1286 ft Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-585 B-586 B-586 RIC-10A RIC-10A RIC-1042 RIC-142 RIC-143 RIC-145 RIC-145 RIC-145 RIC-145 B-513 B-550 B-550 B-560A	he file size of the recorded data is limited up to 468.) /s (µs) //s (µs) //s (µs) //s (ys) //s (ys)			
\$50 modulo 6 Model number Storage device Capacity (*23) \$ Sampling speed (*24)(*25) \$ External dimer weight (*25) \$ External d	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 30 modules stoons (W x D x H) cessories ogic input file probe - BNC (C - BNC unana - BNC small size) (*26) "26) able for GL or (*27) ce or, screw terminal ng bracket e	Solid state disk C Approx. 1286 B (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-585 B-586 RIC-101A RIC-101A RIC-104 RIC-104 RIC-104 RIC-105 RIC-105 RIC-105 RIC-106 RI	In the file size of the recorded data is limited up to 468.) /s (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Poise module (GL7-UP), 4 channels, Cable with Alligator clip and IC clip insulated, 1.2 m long, 300 v DC, CAT II. Insulated, 1.5 m long, 1000 v DC, CAT II. Insulated, 1.6 m long, 1000 v DC, CAT II. For RIC-143, Aperture 11 mm, 300 v DC, CAT III. For RIC-143/RIC-147, Aperture 20 mm, 1000 v DC, CAT III. Max. 15 A. For RIC-143/RIC-147, Aperture 20 mm, 1000 v DC, CAT III. Max. 1.4 2 m long, Bare wire for signal connection - Connector for GL series 3 m cables for signal and power 250 ohms (Converts signal from "4-20mA" to "1-5v".) Screw terminal for sensor - D-508 (rectangular connector) for GL7-DCB module For rela-control-8-500. To mm long For Re-15-08-8-500. To mm long			
SSD module & Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dirner Weight Options and as Item Sync, Cable Carrying tool Storage case Probe set for Lingut cable, Sa Input cable, Ba Input cabl	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 30 modules stoons (W x D x H) cessories ogic input file probe - BNC (C - BNC unana - BNC small size) (*26) "26) able for GL or (*27) ce or, screw terminal ng bracket e	Solid state disk C Approx. 1286 ft Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-585 B-586 B-586 RIC-10A RIC-10A RIC-1042 RIC-142 RIC-143 RIC-145 RIC-145 RIC-145 RIC-145 B-513 B-550 B-550 B-560A	the file size of the recorded data is limited up to 46B.) /s(1 µs) /s(2 µs) /s(8/5 (2 µs) /s(8/5 (2 µs) /s(8/5 (2 µs) /s(8/5 (3 µs) /s			
SSD module & Model number Storage device Capacity (*23) Sampling speed (*24)(*25) External dirner Weight Options and as Item Sync, Cable Carrying tool Storage case Probe set for Linput cable, Balinput cab	Attached to 1 or 2 modules Attached to 3 or 4 modules Attached to 3 or 4 modules Attached to 5 to 30 modules Attached to 15 to 30 modules stons (W x D x H)	Solid state disk C Approx. 1286 B (1 Max. 1 M Sample. Max. 500 k Samp Max. 200 k Samp Approx. 49 x 136 Approx. 770 g Model number B-559 B-585 B-585 B-586 RIC-101A RIC-101A RIC-104 RIC-104 RIC-104 RIC-105 RIC-105 RIC-105 RIC-106 RI	In the file size of the recorded data is limited up to 46B.) /s (1 μs) lide/s (2 μs) lide/s (5 μs) x 180 mm (Excluding projection) Remarks 1 m long, Synchronizing between GL7000 Can carry GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules attached. Can store GL7000 with up to 3 modules. Not for transferring. The caster can work only on smooth surface. For Logic/Poise module (GL7-L/P), 4 channels, Cable with Alligator clip and IC clip Insulated, 1.2 m long, 300 v DC, CAT II. Insulated, 1.5 m long, 1000 v DC, CAT II. Insulated, 1.6 m long, 1000 v DC, CAT II. For RIC-143, Aperture 11 mm, 300 v DC, CAT III. For RIC-143/RIC-147, Aperture 20 mm, 1000 v DC, CAT III. Max. 15 A. For RIC-143/RIC-147, Aperture 20 mm, 1000 v DC, CAT III. Max. 1.4 2 m long, Bare wire for signal connection - Connector for GL series 3 m cables for signal and power 250 ohms (Converts signal from "4-20mA" to "1-5v".) For BC CST and module (GL7-DCB). Screw terminal for sensor - D-508 (rectangular connector) for GL7-DCB module For replacement use for B-560/R-560A.			

GL-Connection

(*23) Capacity of memory device may be smaller than above depending on time of production. The file for recording data is limited up to 4GB on firmware version 2.0 or later, 2GB on firmware version 1.6 or before.

(*24) The sampling speed in the G17000 is limited to the faster sampling speed of attached input module. When the selected sampling speed in the G17000 is faster than the module, the sampling is done in fastest sampling on the module. The same value is stored to the memory device in the selected sampling speed until data is renewed by the next sampling. (*25) When the sampling speed in the G17000 is selected to the 1 MS/s (1 µs) or 500 kS/s (2 µs). the number of available channels in the Logic/Pulse module will be limited.

(*26) Red and black [per 1 unit). Connectable with Ric-143, RiC-147.

The data loss caused by the equipment / PC failure is not guaranteed. Please make sure to back up your data, registered frademarks or their respective owners. I tens mentioned are subject to change without notice. For more information about product, please check the web site or contact your local representative.



Model name

For safe and correct use of equipment

Before using it, please read the user manual and then please use it properly in accordance with the description.
 To avoid an occurrence of malfunction or an electric shock by leakage,

please ensure ground connection and use in specified power source.

GRAPHTEC Graphtec America, Inc.

17462 Armstrong Avenue Irvine, CA 92614



